

Ceiling Pull Unit

Part No. **QT607**



Overview

Can be used to generate a Standard or Ensuite call on aQuantec Addressable Call System.

Typically wired as a slave to aQuantec Addressable Call Point or Quantec Accessible Toilet Reset Point.

Supplied with 3m of red nylon pull cord and two red open-sided triangular bangles for ease of use by the infirm.

Red confidence LED and diffuser emits a bright red glow over a wide area to reassure the user that a call has been made.

Surface mountable.

Base fits 16mm conduit and BESA centres.

Also available as part of the QT951 Accessible Toilet Expansion Kit.

Technical Specifications

Quiescent current	Less than 3mA.
Alarm current	6mA.
Indicators	Red reassurance LED/diffuser (active in Alarm).
Controls	Red pull cord (activated by pulling one of the QT607's bangles).
Connections	Local +V; S (Switch); R (Red). Wire as a slave to a Quantec Addressable Call Point or Accessible Toilet Reset Point. See instructions for details.
Onboard Sounder	No.
Product dimensions (mm)	93mm diameter x 27mm deep. Designed for ceiling mounting only. Base fits 16mm conduit and BESA centres.
Construction & finish	Plastic.
IP Rating	IP21.
Weight	56g.
Operating conditions/temperature	-5°C to +40°C. Max. relative humidity 95% non-condensing.



T 01942 322744 **E** sales@c-tec.co.uk
F 01942 829867 **W** www.c-tec.com



C-TEC, Challenge Way, Martland Park, Wigan, WN5 0LD United Kingdom