

Quantec Slave Infrared Ceiling Receiver (Round Version)

Part No. **QT302RXRS**



Overview

An unobtrusive white roundslave infrared receiver.

Connects to a master Quantec infrared receiving device to increase IR coverage.

Designed to accept infrared calls from compatible Quantec staff attack transmitters, patient neck/wrist pendants and staff attendance pendants.

Typically used in bedrooms, corridors, common rooms and any other area requiring infrared coverage.

Typical 10m line of sight receiving range.

Up to three QT302RXRS slave receivers can be used permaster.

Optional QT848/10 locking kit, complete with 10 grub screws and Allen key, also available.

Technical Specifications

Power requirements	TBC.
Quiescent current	TBC.
Indicators	Red/green confidence LED/diffuser.
Controls	n/a.
Connections	N+: N-; R; G; L+; IR. Wire as a slave to a Quantec Addressable Call Point or Master Infrared Ceiling Receiver. See instructions for details.
Onboard 6.35mm Remote Jack Socket	No.
Onboard Sounder	No.
Onboard Infrared Receiver	Yes - will accept calls from compatible Quantec infrared transmitters.
Product dimensions (mm)	93mm diameter x 27mm deep. Designed for ceiling mounting only. Base fits 16mm conduit and BESA centres.
Construction & finish	White round plastic.
IP Rating	TBC.
Weight	TBC.



Operating conditions/temperature

-5°C to +40°C. Max relative humidity: 95%.

Notes

Optional QT848/10 locking kit, complete with 10 grubscrews and Allen key, available.



T 01942 322744

E sales@c-tec.co.uk

F 01942 829867

W www.c-tec.com



C-TEC, Challenge Way, Martland Park, Wigan, WN5 0LD United Kingdom



T 01942 322744 **E** sales@c-tec.co.uk
F 01942 829867 **W** www.c-tec.com



C-TEC, Challenge Way, Martland Park, Wigan, WN5 0LD United Kingdom